



DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____

Incandescent

P5414-30

Mansard

Post lantern with ribbed mansard roof. Beveled clear acrylic panels. Polypropelene construction. Post top fits 3" post or pedestal mount.

Category: Outdoor

Finish: White

Construction: Polypropelene construction construction

Glass: Clear beveled acrylic panels



Diameter: 8"
Height: 12-19/32"

Glass: Top width 5-5/16", Bottom width 3-1/8"
Height: 5.28"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Post top mounted Mounting strap for outlet box included	Pre-wired 6" of wire supplied 120V	Quantity: 1 60W Medium Base Medium phenolic socket	UL-CUL Wet location listed 1 year warranty Companion Post top lantern, Wall lantern fixtures are available