

# One-Light Outdoor

 Post mounted • Wet location listed **PROGRESS LED**


## Description:

Westport LED offers traditional styling to complement a variety of home decor options. A durable die-cast aluminum frame cradles a softly diffused seeded glass shade. 3000K, 90+ CRI 623 lumens. One-light LED post mount. Antique Bronze finish.

## Specifications:

- Antique Bronze (-20) (powder coat paint)
- Die-Cast Aluminum Construction
- Etched Seeded glass shade
- LED Module is replaceable (part # 93054049)
- Traditional styling.
- Softly diffused seeded glass shade.
- Complements many home decor styles with beaded detailing.
- 623 lumens 69.2 lumens/watt (source)
- 3000K color temperature, 90+ CRI.
- Dimmable to 10% brightness (See Dimming Notes)
- 6" of wire supplied
- ENERGY STAR® qualified
- Meets California Title 24 high efficacy requirements for outdoor use only

## Performance:

|                        |                                                                                                                                      |
|------------------------|--------------------------------------------------------------------------------------------------------------------------------------|
| Number of Modules      | 1                                                                                                                                    |
| Input Power            | 9w                                                                                                                                   |
| Input Voltage          | 120 V                                                                                                                                |
| Input Frequency        | 60 Hz                                                                                                                                |
| Lumens/LPW (Source)    | 623/69.2 (LM-82)                                                                                                                     |
| Lumens/LPW (Delivered) | 357/47.6 (LM-79)                                                                                                                     |
| CCT                    | 3000 K                                                                                                                               |
| CRI                    | 90 CRI                                                                                                                               |
| Life (hours)           | 60,000 (L70/TM-21)                                                                                                                   |
| FCC                    | Meets FCC Title 47, Part 15 Class B                                                                                                  |
| Min. Start Temp        | -30 °C                                                                                                                               |
| Max. Operating Temp    | 30 °C                                                                                                                                |
| Warranty               | 5 year warranty                                                                                                                      |
| Labels                 | cCSAus Wet location listed<br>ENERGY STAR® qualified<br>Meets California Title 24 high efficacy requirements<br>for outdoor use only |

## P5445-2030K9

## Images:



## Dimensions:

Diameter: 9"  
Height: 16-3/8"

Diffuser  
Width: 7"  
Length: 7"  
Height: 5-3/4"

## P5445-2030K9

### Dimming Notes:

---

P5445 is designed to be compatible with many ELV/Reverse Phase controls.

The following is a partial list of known compatible dimmer controls.

### Dimming Controls

---

|         |               |            |
|---------|---------------|------------|
| Lutron  | Nova T        | NTELV-300  |
| Lutron  | Vierti        | VTELV-600  |
| Lutron  | Ariadni       | AYCL-153P  |
| Lutron  | Diva          | DVCL-153P  |
| Lutron  | Maestro       | MAELV-600  |
| Lutron  | spacer/system | SPSELV-600 |
| Leviton | Renoir II     | AWRMG-EAW  |

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation. Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.