

DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____

Incandescent

P5456-31

Non-Metallic Incandescent

Set this sculpted post lantern near your walkway to guide guests inside, or let it light up a patio for outdoor gatherings. Its crystal clear acrylic panels stand up to harsh weather, and 100-watt lighting provides brilliant, far-reaching illumination. Non-metallic post lantern with clear, beveled acrylic panels in a Black finish.

- Black finish.
- Clear beveled acrylic panels.
- Non-metallic.
- Post lantern requires one 100-watt incandescent bulb
- UL listed for safety

Category: Outdoor

Finish: Black (painted)

Construction: Polypropylene Construction

Glass/Shade: Clear Beveled acrylic panels



Diameter: 7-3/4"

Height: 17-5/8"

Glass

Width: 5-5/16"

Height: 5-1/2"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Post top - fitter for 3" post or pedestal mounted Mounting No for outlet box included	Pre-wired 6" of wire supplied 120 V	Quantity: One 100w max. Medium Base E26 base porcelain socket	UL-CUL Wet location listed 1 year warranty