

DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____

Incandescent

P550005-031

Pier 33

The one-light hanging lantern from the Pier 33 collection features coastal undertones and a design reminiscent of industrial spaces. Comprised of a die-cast frame with clear seeded glass and a Black finish.

- Black finish
- Coastal undertone
- Design reminiscent of industrial spaces
- Clear seeded glass

Category: Outdoor

Finish: Black (painted)

Construction: Die-cast aluminum construction

Glass/Shade: Clear seeded glass globe



Diameter: 8-1/8"

Height: 13-1/4"

Overall Ht. W/Chain: 79-1/2"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling mounted Mounting strap for outlet box included Six links of 9 gauge chain supplied One 6", four 12" lengths of stem included Canopy covers a standard 4" hexagonal recessed outlet box 5" W., 1" depth	Pre-wired 10 feet of wire supplied 120 V	Quantity: One 100w max. Medium Base E26 base ceramic socket	cULus Damp location listed 1 year warranty