

DATE:

TYPE:

NAME:

PROJECT:

Incandescent

P550009-031

Creighton

A cottage-inspired outdoor hanging lantern collection with a tapered cage. Creighton features clear water glass clear and Black finish. The frame's linear details are riveted to enhance mechanical detailing of the fixture. Wall, post and hanging lantern options available.

- Black finish
- Cottage-inspired outdoor lantern
- Features a tapered cage design
- Clear water glass panels
- Linear details enhance mechanical detailing of fixture

Category: Outdoor

Finish: Black (painted)

Construction: Aluminum construction

Glass/Shade: Clear water glass panels



Diameter: 10-1/2" Height: 21-5/8" Overall Ht. W/Chain: 96-1/2"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling mounted	Pre-wired	Quantity:	cULus Damp location listed
Mounting strap for outlet box included Six feet of 9 gauge chain supplied	10 feet of wire supplied 120 V	One 100w max. Medium Base E26 base ceramic socket	1 year warranty
Canopy covers a standard 4" hexagonal recessed outlet box 5" W., 0.875" depth			