

DATE:	TYPE:	
NAME:		
PROJECT:		

## Incandescent

## P550022-129

## Laine

Laine features a cylindrical frame accented with clear glass and metallic elements. Traditional Architectural Bronze profile is paired with vintage gold accents. Wall lantern option features arm that resembles a pipe fitting, offering an industrial-inspired appeal.

- Laine features a cylindrical frame accented with a clear glass diffuser
- Outdoor lanterns add illumination to walkways and pathways to enhance safety and security
- Traditional Architectural Bronze profile is paired with vintage gold accents
- Industrial-inspired design
- Lantern uses one 100 watt max. medium base bulb, (sold separately)
- Frame front or back door with post lanterns on either side to enhance curb appeal
- Suitable for a variety of exteriors
- Frame front or back door with hanging lanterns on either side to enhance curb appeal
- Suitable for a variety of exteriors
- Can also be used in interior settings and paired with decorative fixtures for creative design ideas.

Category: Outdoor Finish: Architectural Bronze (painted) Construction: Aluminum construction Glass/Shade: Clear Glass				
MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION	
Hanging mounted	10 feet of wire supplied	Quantity:	cULus Damp location listed	
Mounting strap for outlet box included  Six feet of 9 gauge chain supplied	120 V	One 100w max. Medium Base E26 base	1 year limited warranty	
Canopy covers a standard 4" octagonal recessed outlet box 5.25" W., 1" ht., 5.25" depth				



Diameter: 9-3/4" Height: 15-7/8"

Overall Ht. W/Chain: 91"

Glass

Width: 7-7/8" Height: 12-1/4"