

DATE:	TYPE:	
NAME:		
PROJECT:		

Incandescent

P550041-103

Morrison

The Morrison Collection hanging lantern blends delicate geometric patterns with lasting durability in a modern form. Intricate die cast aluminum construction is paired with clear glass and an Antique Pewter finish.

- Swirling metallic accents covering a clear-glass shade are an ornamental addition to your home's exterior and its surrounding landscape
- The hanging lantern makes a cheerful greeting in a portico over an entry door, or hung in multiples from the roof of a porch or veranda
- Morrison's construction and design complements both Modern and Traditional architecture
- Stately Antique Pewter finish
- Measures 7 1/2in diameter x 22in ht. x 7 1/2in D
- Uses one 100-watt max. medium base bulb including LED equivalent (sold separately)
- CSA Safety listed for use in damp locations
- Compatible with standard wall dimmer
- Progress Lighting products are designed for exceptional quality, reliability, and functionality
- Includes installation instructions and mounting hardware
- Coordinating fixtures available

Category: Outdoor

Finish: Antique Pewter (plated)

Construction: Die-Cast Aluminum Construction

Glass/Shade: Clear glass cylinder

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling mounted	Pre-wired	Quantity:	cCSAus Damp location listed
Mounting strap for outlet box included Six feet of 9 gauge chain supplied	10 feet of wire supplied 120 V	One 100w max. Medium Base E26 base porcelain socket	1 year warranty
Canopy covers a standard 4" octagonal recessed outlet box 5" W., 1" ht., 5" depth			



Diameter: 7-1/2" Height: 22" Depth: 7-1/2"

Overall Ht. W/Chain: 95"

Width: 5-7/8" Height: 11-7/16"