

Project: _____

Fixture Type: _____

Location: _____

Contact: _____

P550044-108 Janssen

Create a home full of modern elegance with this contemporary hanging lantern. A sleek elongated frame with a rectangular form manifests an architectural design intended to add a modern glow while commanding visual interest. The light fixture features a gorgeous etched glass diffuser ready to emit a beautiful glow.

- The light fixture features a gorgeous etched glass diffuser ready to emit a beautiful glow.
- A sleek elongated frame with a rectangular form manifests an architectural design intended to add a modern glow while commanding visual interest.
- Create a home full of modern elegance with this contemporary hanging lantern.
- Ideal for any foyer, entryway, porch, or patio.
- Perfect for modern or contemporary styles.
- Measures 7-1/2-inch width by 21-inch height.
- Uses one medium base bulb that is sold separately (100w max - LED or incandescent).
- Able to be fully dimmable with dimmable bulbs.
- Includes installation instructions and mounting hardware.
- Progress Lighting products are designed for exceptional quality, reliability, and functionality.

Category: Outdoor

Finish: Oil Rubbed Bronze (Painted)

Construction: Aluminum Construction

Glass/Shade: Etched glass Cylindrical Shade



Diameter: 7-1/2 in
Height: 21 in
Overall Ht. W/Chain: 96 in

Etched glass Cylindrical Shade
Width: 4-1/2 in
Height: 12 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling chain mounted	Prewired	Quantity:	CULus Damp Location Listed
1/8 IP mounting plate for outlet box included	10 feet of wire supplied	One 100 W max. Medium Base or LED equivalent	1-year Limited Warranty
6 feet of 9 gauge chain supplied	120 V	E26 base Porcelain socket	
Canopy covers a standard 4" recessed outlet box: 5.125" W., 5.125" ht., 1" depth			