## **PROGRESS** LIGHTING<sup>™</sup>

Project:		
Fixture Type:		

Location:

Contact:

## P550058-020 Trellis

Create a home that is undeniably beautiful with the intricate craftsmanship of this-nature-inspired hanging lantern. Beautiful white art glass panels serve as a backdrop to carefully crafted twig silhouettes. The panels are housed in a handsome antique bronze frame that will capture the gazes and hearts of both family members and guests.

- Beautiful white art glass panels serve as a backdrop to carefully crafted twig silhouettes.
- The panels are housed in a handsome antique bronze frame that will capture the gazes and hearts of both family members and guests.
- Create a home that is undeniably beautiful with the intricate craftsmanship of this-nature-inspired hanging lantern.
- Ideal for any entryway, patio, or porch.
- Perfect for rustic or Craftsman settings.
- Measures 7-1/2-inch width by 13-1/2-inch height.
- Uses one medium base bulb that is sold separately (100w max LED or incandescent).
- Able to be fully dimmable with dimmable bulbs.
- Includes installation instructions and mounting hardware.
- Progress Lighting products are designed for exceptional quality, reliability, and functionality.

Category: Outdoor Finish: Antique Bronze (Painted) Construction: Steel Construction Glass/Shade: White Art glass Panel



Square: 7-1/2 in Height: 13-1/2 in Overall Ht. W/Chain: 88-1/2 in

White Art glass Panel Width: 5-3/4 in Height: 10-5/8 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling chain mounted	Prewired	Quantity: One 100 W max. Medium Base or	CULus Damp Location Listed
1/8 IP mounting plate for outlet box included	10 feet of wire supplied	LED equivalent	1-year Limited Warranty
	120 V	E26 base Porcelain socket	
6 feet of 9 gauge chain supplied			

Canopy covers a standard 4" recessed outlet box: 5" W., 1" ht., 5" depth