

Project: _____

Fixture Type: _____

Location: _____

Contact: _____

P550061-031

Port Royal

This hanging lantern distills both industrial and artisan influences with its signature ribbed black frame constructed from durable corrosion-resistant, composite polymer. Inside the ribs rests an elongated, clear glass shade that adds to the light fixture's modern flair. The design's blend of industrial and coastal inspiration makes it a perfect light fixture for updating your favorite spaces in and around your home. DURASHIELD by Progress Lighting is built to last. Constructed from a composite material with UV protection, DURASHIELD holds up even in the harshest weather conditions. This high-performance finish has a 5-year warranty and is resistant to rust, corrosion, and fading.

- Inside the ribs rests an elongated, clear glass shade that adds to the light fixture's modern flair.
- This hanging lantern distills both industrial and artisan influences with its signature ribbed black frame constructed from durable corrosion-resistant, composite polymer materials.
- Ideal for any foyer, entryway, patio, or porch in urban industrial, farmhouse, or coastal settings.
- DURASHIELD by Progress Lighting is a material that is built to last. Constructed from a composite polymer with UV protection, DURASHIELD holds up even in the harshest weather conditions. This high-performance material has a 5-year warranty and is resistant to rust, corrosion, and fading.
- Measures 6-1/4-inch width by 14-inch height.
- Uses one medium base bulb that is sold separately (60w max - LED or incandescent).
- Able to be fully dimmable with dimmable bulbs.
- Includes installation instructions and mounting hardware.
- Progress Lighting products are designed for exceptional quality, reliability, and functionality.

Category: Outdoor

Finish: Black (Painted)

Construction: Composite Polymer Construction

Glass/Shade: Clear glass Cylindrical Shade



Diameter: 6-1/4 in
Height: 14 in
Overall Ht. W/Chain: 86-1/2 in

Clear glass Cylindrical Shade
Width: 4-5/8 in
Height: 9-3/16 in

| MOUNTING | ELECTRICAL | LAMPING | ADDITIONAL INFORMATION |
|--|--------------------------|---|-----------------------------|
| Ceiling chain mounted | Prewired | Quantity: | CETLus Damp Location Listed |
| 1/8 IP mounting plate for outlet box included | 10 feet of wire supplied | One 60 W max. Medium Base or LED equivalent | 5-year Limited Warranty |
| 6 feet of 9 gauge chain supplied | 120 V | E26 base Porcelain socket | |
| Canopy covers a standard 4" recessed outlet box: 5" W., 5" ht., 1.125" depth | | | |