

Project: _____

Fixture Type: _____

Location: _____

Contact: _____

P550064-020 Grandbury

Grandbury Collection One-Light Transitional Antique Bronze Clear Glass Outdoor Hanging Light with DURASHIELD

Category: Outdoor

Finish: Antique Bronze (Unfinished)

Construction: injection-Molded Plastic Construction

Glass/Shade: Clear Glass Panel



Square: 7 in
Height: 15-3/8 in
Overall Ht. W/Chain: 90-1/2 in

Clear Glass Panel

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Chain	10 feet of wire supplied	(1) Medium Base (E26) Socket	cULus Damp Location Listed
1/8 IP mounting plate for outlet box included	120 VAC	Lamp Type A19	5-year Limited Warranty
6 feet of 9 Gauge chain supplied		Incandescent: 75-watt MAX per socket LED: 15-watt MAX per socket	
Canopy covers a standard 4" recessed outlet box: 5.125" W., 5.125" ht., 0.75" depth		Fully dimmable with dimmable bulbs	