

Project:			
Fixture Type:			
Location:			
C			

P550065-031

Benton Harbor

This hanging lantern is expertly crafted with that casual, coastal style you love. A clear glass shade shields a simple light base for a seaside-living vibe. The shade is cradled inside an open-cage black frame featuring thin bars and constructed with a composite polymer, corrosion-resistant housing. DU-RASHIELD by Progress Lighting is built to last. Constructed from a composite material with UV protection, DURASHIELD holds up even in the harshest weather conditions. This high-performance finish has a 5-year warranty and is resistant to rust, corrosion, and fading.

- · A clear glass shade shields a simple light base for a seaside-living vibe.
- The glass shade is cradled inside an open-cage black frame of corrosion-proof composit polymer.
- \cdot The hanging lantern is expertly crafted with a non-metallic, corrosion-resistant housing.
- Ideal for any foyer, entryway, porch, or patio in transitional or coastal settings.
- DURASHIELD by Progress Lighting is a material that is built to last. Constructed from a
 composite polymer with UV protection, DURASHIELD holds up even in the harshest weather conditions. This high-performance material has a 5-year warranty and is resistant to rust,
 corrosion, and fading.
- Measures 8-3/4-inch width by 13-1/4-inch height.
- Uses one medium base bulb that is sold separately (75w max LED or incandescent).
- · Able to be fully dimmable with dimmable bulbs.
- · Includes installation instructions and mounting hardware.
- · Progress Lighting products are designed for exceptional quality, reliability, and functionality.

Category: Outdoor Finish: Black (Painted)

Construction: Composite Polymer Construction

Glass/Shade: Clear glass Shade



Diameter: 8-3/4 in Height: 13-1/4 in

Overall Ht. W/Chain: 93-1/2 in

Clear glass Shade Width: 7-7/8 in Height: 8-3/16 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling chain mounted	Prewired	Quantity: One 75 W max. Medium Base or	CETLus Damp Location Listed
1/8 IP mounting plate for outlet box included	10 feet of wire supplied	LED equivalent	5-year Limited Warranty
	120 V	E26 base Porcelain socket	
6 feet of 9 gauge chain supplied			
Canopy covers a standard 4" recessed outlet box: 5.125" W., 5.125" ht., 0.75" depth			