

Project: _____

Fixture Type: _____

Location: _____

Contact: _____

P550070-079 Cedar Springs

This fun take on the traditional warehouse shade provides excellent task lighting. Take in the simple metal shade coated in a gorgeous pistachio finish ready to direct a helpful glow. An industrial-style ceiling plate anchors the light fixture in place and adds a touch of urban flair.

- Take in the simple metal shade coated in a gorgeous pistachio finish ready to direct a helpful glow.
- An industrial-style ceiling plate anchors the light fixture in place and adds a touch of urban flair.
- This fun take on the traditional warehouse shade provides excellent task lighting.
- Ideal for any hallway, entryway, porch, or patio.
- Perfect for urban industrial, rustic, farmhouse, and coastal settings.
- Measures 13-1/4-inch width by 9-1/2-inch height.
- Uses one medium base bulb that is sold separately (100w max - LED or incandescent).
- Able to be fully dimmable with dimmable bulbs.
- Includes installation instructions and mounting hardware.
- Progress Lighting products are designed for exceptional quality, reliability, and functionality.

Category: Outdoor

Finish: Pistachio (Painted)

Construction: Aluminum Construction



Diameter: 13-1/4 in
Height: 9-1/2 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling mounted	Prewired	Quantity: One 100 W max. Medium Base or LED equivalent	CCSAus Damp Location Listed 1-year Limited Warranty
Mounting plate for outlet box included	6 inches of wire supplied	E26 base Porcelain socket	
Canopy covers a standard 4" recessed outlet box: 5" W., 2.18" ht., 5" depth	120 V		