## **PROGRESS** LIGHTING<sup>™</sup>

Project: Fixture Type: Location:

Contact:

## P550093-135 Tremont

Tremont Collection 1-Light Stainless Steel Clear Seeded Glass Farmhouse Mini-Pendant Hanging Light

## Category: Outdoor

Finish: Stainless Steel (Plated) Construction: Stainless Steel Construction Glass/Shade: Clear Seeded Glass Cylindrical



Length: 9 in Diameter: 9 in Height: 8 in Overall Ht. W/Chain Or Stem: 77 in

Clear Seeded Glass Cylindrical Width: 4-3/837 in Height: 7-9/16 in

	0		
MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Stem Hung with 6 links of chain	10 feet of wire supplied	Quantity: one 60 W max.	cULus Damp Location Listed
chain	120 V		1-year Limited Warranty
Mounting plate for outlet box included		E26 base Porcelain Socket	
six links of 9 gauge chain supplied			
one 6", four 12" lengths of stem included			

Canopy covers a standard 4" recessed outlet box: 5.125" W., 5.125" ht., 1" depth