

### Project:

Fixture Type:

Location: Contact:

# **5IN CYL RNDS**

### Ceiling Cord Mounted • Damp Location Listed PROGRESS LED

#### **Description:**

Cylinder Collection 5-Inch 1-Light Black LED Modern Outdoor Pendant Hanging Light

#### **Specifications:**

- Dimmable to 10% brightness (See Dimming Notes)
- Canopy covers a standard 4" recessed outlet box: 4.72 in W., 0.79 in ht., 4.72 in depth
- + Mounting strap for outlet box included
- + 6 in of wire supplied

#### Performance:

Number of Modules	1
Input Power	18.6 W
Input Voltage	120 VAC
Input Frequency	60 Hz
Lumens/LPW (Delivered)	468/25 (LM-79)
CCT	3000 K
CRI	90 CRI
Life (hours)	50000 (L70/TM-21)
EMI/RFI	FCC Title 47, Part 15, Class B
Warranty	5-year Limited Warranty
Labels	cCSAus Damp Location Listed



#### **Dimensions:**

Length: 5 in Diameter: 5 in Height: 9-13/16 in Overall Ht. W/Cord: 128.04 in



## **5IN CYL RNDS**

Ceiling Cord Mounted • Damp Location Listed PROGRESS LED

#### **Dimming Notes:**

 $\mathsf{P550099}\text{-}031\text{-}30$  is designed to be compatible with many ELV/Reverse Phase controls.

The following is a partial list of known compatible dimmer controls.

#### **Dimming Controls:**

Lutron NTEVL-300

Lutron DVELV-300P

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation.

Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.

