

## 6IN CYL RNDS

Ceiling Cord Mounted • Damp Location Listed **PROGRESS LED**

### Description:

Cylinder Collection 6-Inch 1-Light Antique Bronze LED Modern Outdoor Pendant Hanging Light

### Specifications:

- Dimmable to 10% brightness (See Dimming Notes)
- Canopy covers a standard 4" recessed outlet box: 4.72 in W., 0.79 in ht., 4.72 in depth
- Mounting strap for outlet box included
- 120 in of wire supplied

### Performance:

Number of Modules	1
Input Power	32 W
Input Voltage	120 VAC
Input Frequency	60 Hz
Lumens/LPW (Delivered)	930/29 (LM-79)
CCT	3000 K
CRI	90 CRI
Life (hours)	50000 (L70/TM-21)
EMI/RFI	FCC Title 47, Part 15, Class B
Warranty	5-year Limited Warranty
Labels	cCSAus Damp Location Listed

# P550100-020-30



### Dimensions:

Length: 6 in  
Diameter: 6 in  
Height: 12 in  
Overall Ht. W/Cord: 132.8 in

# P550100-020-30

## Dimming Notes:

---

P550100-020-30 is designed to be compatible with many ELV/Reverse Phase controls.

The following is a partial list of known compatible dimmer controls.

## Dimming Controls:

---

Lutron NTEVL-300

Lutron DVELV-300P

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation.

Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.