

5IN CYL RNDS

Wall Mounted • Wet Location Listed PROGRESS LED

Description:

Cylinder Collection 1-Light Antique Bronze 5-Inch Modern Outdoor Small Wall Lantern Light

Specifications:

- Dimmable to 10% brightness (See Dimming Notes)
- Canopy covers a standard 4" recessed outlet box: 4.45 in W., 4.45 in ht., 0.65 in depth
- Mounting backplate for outlet box included
- 6 in of wire supplied

Performance:

Number of Modules	1
Input Power	18.6 W
Input Voltage	120 VAC
Input Frequency	60 Hz
Lumens/LPW (Delivered)	511/27 (LM-79)
CCT	3000 K
CRI	90 CRI
Life (hours)	50000 (L70/TM-21)
EMI/RFI	FCC Title 47, Part 15, Class B
Warranty	5-year Limited Warranty
Labels	cCSAus Wet Location Listed

P550101-020-30



Dimensions:

Length: 5 in
Depth: 7-15/16 in
Height: 7-1/4 in

P550101-020-30

Dimming Notes:

P550101-020-30 is designed to be compatible with many ELV/Reverse Phase controls.

The following is a partial list of known compatible dimmer controls.

Dimming Controls:

Lutron NTEVL-300

Lutron DVELV-300P

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation.

Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.