

Project: \_\_\_\_\_

Fixture Type: \_\_\_\_\_

Location: \_\_\_\_\_

Contact: \_\_\_\_\_

## P550109-31M

### Whitmire

Whitmire Collection One-Light Matte Black with Aged Oak Accents Clear Seeded Glass Farmhouse Outdoor Ceiling Mount Light

**Category:** Outdoor

**Finish:** Matte Black (Painted) with Aged Oak accent

**Construction:** Steel Construction

**Glass/Shade:** Clear Seeded Glass Cylindrical



Diameter: 7-3/8 in  
Height: 8 in

Clear Seeded Glass Cylindrical  
Length: 5-1/8 in  
Width: 5-1/8 in  
Height: 6-1/2 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling semi-flush	6 inches of wire supplied	(1) Medium Base (E26) Socket	cULus Damp Location Listed
Swivel mounting strap for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
Canopy covers a standard 4" recessed outlet box: 5.12" W., 5.12" ht., 0.75" depth		Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket Fully dimmable with dimmable bulbs	