

Project:

Fixture Type:

Location:

Contact:

## P550111-31M

## **Terrace**

Terrace Collection One-Light Matte Black Clear Seeded Glass Global Outdoor Hanging Light

Category: Outdoor

Finish: Matte Black (Painted) with Antique Bronze accent

Construction: Steel Construction

Glass/Shade: Clear Seeded Glass Cylindrical



Diameter: 17-7/8 in Height: 20-1/2 in Overall Ht. W/Chain: 101 in

overall tit. Wy chain. For in

Clear Seeded Glass Cylindrical Width: 4-5/16 in Height: 17-15/16 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Chain	10 feet of wire supplied	(1) Medium Base (E26) Socket	cULus Damp Location Listed
1/8 IP mounting plate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
6 feet of 9 Gauge gauge chain		Incandescent: 60-watt MAX per	
supplied (1)		LED: 12.5-watt MAX per socket	
Canopy covers a standard 4" recessed outlet box: 5.12" W., 1" ht., 5.12" depth		Fully dimmable with dimmable bulbs	