

## Hard Nox

Ceiling Mounted • Wet Location Listed **PROGRESS LED**

# P550113-028-30

### Description:

Hard Nox Collection White 12" Square Flush Mount Light

### Specifications:

- White Acrylic Diffuser
- Dimmable to 10% brightness (See Dimming Notes)
- Ceiling Pan covers a standard 4" recessed outlet box
- Housing
- 6 in of wire supplied

### Performance:

Number of Modules	1
Input Power	25 W
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW (Delivered)	2,136/85 (LM-79)
CCT	3000 K
CRI	90 CRI
Life (hours)	50000 (L70/TM-21)
EMI/RFI	FCC Title 47, Part 15, Class B
Warranty	5-year Limited Warranty
Labels	UL Wet Location Listed Meets California Title 24 JA8-2016



### Dimensions:

Square: 10-1/2 in  
 Height: 4 in

White Acrylic Diffuser

# P550113-028-30

## Dimming Notes:

---

P550113-028-30 is designed to be compatible with many ELV/Reverse Phase controls.

The following is a partial list of known compatible dimmer controls.

## Dimming Controls:

---

Leviton 6681

Leviton 6674

Lutron NTEVL-300

Lutron DVELV-300P

Lutron Caseta Wireless

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation.

Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.