

Project:

Fixture Type:

Location:

Hard Nox

Ceiling Mounted • Wet Location Listed PROGRESS LED

Contact:

Description:

Hard Nox Collection White 9" Round Flush Mount Light

Specifications:

- · White Polycarbonate Diffuser
- · Dimmable to 10% brightness (See Dimming Notes)
- $\boldsymbol{\cdot}$ Ceiling Pan covers a standard 4" recessed outlet box
- Housing
- 6 in of wire supplied

Performance:

Number of Modules	1
Input Power	25 W
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW (Delivered)	1,644/65 (LM-79)
ССТ	3000 K
CRI	90 CRI
Life (hours)	50000 (L70/TM-21)
EMI/RFI	FCC Title 47, Part 15, Class B
Warranty	5-year Limited Warranty
Labels	UL Wet Location Listed
	Meets California Title 24 JA8-2016

P550114-028-30



Dimensions:

Diameter: 9-15/16 in Height: 4-3/4 in

White Polycarbonate Diffuser



Hard Nox

Ceiling Mounted • Wet Location Listed PROGRESS LED

Dimming Notes:

P550114-028-30

 $\ensuremath{\mathsf{P550114\text{-}}028\text{-}30}$ is designed to be compatible with many ELV/Reverse Phase controls.

The following is a partial list of known compatible dimmer controls.

Dimming Controls:

Leviton 6681

Leviton 6674

Lutron NTEVL-300

Lutron DVELV-300P

Lutron Caseta Wireless

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation.

Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.