

Project:

-----

Fixture Type:

Location:

Contact:

## Hard Nox

### Ceiling Mounted • Wet Location Listed PROGRESS LED



P550115-028-30

#### **Description:**

Hard Nox Collection White 10" Square Flush Mount Light

#### **Specifications:**

- White Polycarbonate Diffuser
- Dimmable to 10% brightness (See Dimming Notes)
- Ceiling Pan covers a standard 4" recessed outlet box
- Housing
- + 6 in of wire supplied

#### **Performance:**

Number of Modules	1
Input Power	25 W
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW (Delivered)	1,613/64 (LM-79)
ССТ	3000 K
CRI	90 CRI
Life (hours)	50000 (L70/TM-21)
EMI/RFI	FCC Title 47, Part 15, Class B
Warranty	5-year Limited Warranty
Labels	UL Wet Location Listed
	Meets California Title 24 JA8-2016



#### **Dimensions:**

Square: 10 in Height: 4-1/2 in

White Polycarbonate Diffuser



## Hard Nox

Ceiling Mounted • Wet Location Listed PROGRESS LED

#### **Dimming Notes:**

 $\mathsf{P550115}\text{-}028\text{-}30$  is designed to be compatible with many ELV/Reverse Phase controls.

The following is a partial list of known compatible dimmer controls.

#### **Dimming Controls:**

Leviton 6681
Leviton 6674
Lutron NTEVL-300
Lutron DVELV-300P
Lutron Caseta Wireless

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation.

Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.

# P550115-028-30