

Fixture Type:	Project:			
Location:	Fixture Type:			
LOCATION.	Location:			

Contact:

## **P550116-039** Cedar Springs

Cedar Springs Collection One-Light Textured Black Red Metal Shade Farmhouse Outdoor Hanging Light

**Category:** Outdoor **Finish:** Red (Painted)

**Construction:** Steel Construction **Glass/Shade:** Red Metal Shade



Diameter: 13-3/16 in Height: 7-1/2 in

Overall Ht. W/Stem: 65-1/2 in

Red Metal Shade Width: 13-3/16 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Stem Hung with Swivel	10 feet of wire supplied	(1) Medium Base (E26) Socket	cCSAus Damp Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
One 6", four 12" lengths of stem		Incandescent: 100-watt MAX per socket	
included		LED: 17.5-watt MAX per socket	
Canopy covers a standard 4" recessed outlet box: 5" W., 2.187" ht., 5" depth		Fully dimmable with dimmable bulbs	