

Project: _____

Fixture Type: _____

Location: _____

Contact: _____

P550117-141 Point Dume-Hook Pond

Jeffrey Alan Marks Point Dume Hook Pond Galvanized Finish Outdoor Hanging Lantern

Category: Outdoor

Finish: Galvanized Finish (Painted)

Construction: Cast Aluminum Construction

Glass/Shade: Clear with Silver Mesh Print Glass Flat Square/Rectangular, White Opal Glass Globe



Width: 16-1/8 in
Extends: 16-1/8 in
Height: 28-9/16 in
Overall Ht. W/Chain: 101 in

Clear with Silver Mesh Print Glass Flat Square/Rectangular
Width: 12-1/8 in
Height: 15-3/8 in

White Opal Glass Globe
Length: 9 in
Width: 9 in
Height: 9-1/4 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Chain	15 feet of wire supplied	(1) Medium Base (E26) Socket	cETLus Damp Location Listed
1/8 IP mounting plate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
6 feet of 9 Gauge chain supplied with quick link		Incandescent: 100-watt MAX per socket LED: 17.5-watt MAX per socket	
Canopy covers a standard 4" recessed outlet box: 7" W., 1" ht., 7" depth		Fully dimmable with dimmable bulbs	