

Project:

Fixture Type:

Location:

Contact:

P550117-192

Point Dume-Hook Pond

Jeffrey Alan Marks Point Dume Hook Pond Shelter White Outdoor Hanging Lantern

Category: Outdoor

Finish: Shelter White (Painted)

Construction: Cast Aluminum Construction

Glass/Shade: Clear with Silver Mesh Print Glass Flat Square/Rectangular,

White Opal Glass Globe



Width: 16-1/8 in Extends: 16-1/8 in Height: 28-9/16 in Overall Ht. W/Chain: 101 in

Clear with Silver Mesh Print Glass Flat Square/Rectangular

Width: 12-1/8 in Height: 15-3/8 in

White Opal Glass Globe

Length: 9 in Width: 9 in Height: 9-1/4 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Chain	15 feet of wire supplied	(1) Medium Base (E26) Socket	cETLus Damp Location Listed
1/8 IP mounting plate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
		Incandescent: 100-watt MAX per	
6 feet of 9 Gauge chain supplied		socket	
with quick link		LED: 17.5-watt MAX per socket	
Canopy covers a standard 4"		Fully dimmable with dimmable	
recessed outlet box: 7" W., 1" ht., 7" depth		bulbs	