

Project:		
Fixture Type:		
Location:		
Contact:		

## P550118-141

## **Point Dume-Shadmore**

Jeffrey Alan Marks Point Dume Shadmore Galvanized Finish Outdoor Wall Lantern

Category: Outdoor

**Finish:** Galvanized Finish (Painted) **Construction:** Steel Construction

Glass/Shade: Marblized Plastic Square/Rectangular



Width: 26 in Extends: 26 in Height: 31-1/4 in

Overall Ht. W/Chain Or Stem: 97-1/2 in

Marblized Plastic Square/Rectangular

Width: 9 in Height: 16 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Chain	10 feet of wire supplied	(1) Medium Base (E26) Socket	cETLus Damp Location Listed
1/8 IP mounting plate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
66 in of 9 Gauge chain supplied with quick link		Incandescent: 100-watt MAX per socket LED: 17.5-watt MAX per socket	
One 6", four 12" lengths of stem included		Fully dimmable with dimmable bulbs	
Canopy covers a standard 4" recessed outlet box: 7" W., 1" ht., 7" depth			