

Project: _____

Fixture Type: _____

Location: _____

Contact: _____

P550118-31M Point Dume™-Shadmore

Point Dume Shadmore Matte Black Outdoor Hanging Pendant

Category: Outdoor

Finish: Matte Black (Painted)

Construction: Steel Construction

Glass/Shade: Marblized Plastic Square/Rectangular



Width: 26 in
Extends: 26 in
Height: 31-1/4 in
Overall Ht. W/Chain Or Stem: 97-1/2 in

Marblized Plastic Square/Rectangular
Width: 9 in
Height: 16 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Chain	10 feet of wire supplied	(1) Medium Base (E26) Socket	cETLus Damp Location Listed
1/8 IP mounting plate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
66 in of 9 Gauge chain supplied with quick link		Incandescent: 100-watt MAX per socket LED: 17.5-watt MAX per socket	
One 6", four 12" lengths of stem included		Fully dimmable with dimmable bulbs	
Canopy covers a standard 4" recessed outlet box: 7" W., 1" ht., 7" depth			