

Project: \_\_\_\_\_

Fixture Type: \_\_\_\_\_

Location: \_\_\_\_\_

Contact: \_\_\_\_\_

## P550119-108 Point Dume-Edgecliff

Jeffrey Alan Marks Point Dume Edgecliff Oil Rubbed Bronze Outdoor Hanging Pendant

**Category:** Outdoor

**Finish:** Oil Rubbed Bronze (Painted)

**Construction:** Cast Aluminum Construction

**Glass/Shade:** Clear with Silver Mesh Print Glass Panel



Width: 33-1/8 in  
Extends: 22-3/4 in  
Height: 14-1/2 in  
Overall Ht. W/Chain: 32-1/2 in

Clear with Silver Mesh Print Glass Panel  
Width: 20-1/8 in  
Height: 9-1/16 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Chain	10 feet of wire supplied	(3) Medium Base (E26) Socket	cETLus Damp Location Listed
1/8 IP mounting plate for outlet box included	120 VAC	Lamp Type G-25	1-year Limited Warranty
6 feet of 9 Gauge chain supplied with quick link		Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	
Canopy covers a standard 4" recessed outlet box: 16" W., 1.125" ht., 5" depth		Fully dimmable with dimmable bulbs	