

Project: _____

Fixture Type: _____

Location: _____

Contact: _____

P550119-141 Point Dume-Edgecliff

Jeffrey Alan Marks Point Dume Edgecliff Galvanized Finish Outdoor Hanging Pendant

Category: Outdoor

Finish: Galvanized Finish (Painted)

Construction: Cast Aluminum Construction

Glass/Shade: Clear with Silver Mesh Print Glass Panel



Width: 33-1/8 in
Extends: 22-3/4 in
Height: 14-1/2 in
Overall Ht. W/Chain: 32-1/2 in

Clear with Silver Mesh Print Glass Panel
Width: 20-1/8 in
Height: 9-1/16 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Chain	10 feet of wire supplied	(3) Medium Base (E26) Socket	cETLus Damp Location Listed
1/8 IP mounting plate for outlet box included	120 VAC	Lamp Type G-25	1-year Limited Warranty
6 feet of 9 Gauge chain supplied with quick link		Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	
Canopy covers a standard 4" recessed outlet box: 16" W., 1.125" ht., 5" depth		Fully dimmable with dimmable bulbs	