

Project:		
Fixture Type:		
Location:		
Contact:		

## P550119-192

## **Point Dume-Edgecliff**

Jeffrey Alan Marks Point Dume Edgecliff Shelter White Outdoor Hanging Pendant

Category: Outdoor

Finish: Shelter White (Painted)

Construction: Cast Aluminum Construction

Glass/Shade: Clear with Silver Mesh Print Glass Panel



Width: 33-1/8 in Extends: 22-3/4 in Height: 14-1/2 in

Overall Ht. W/Chain: 32-1/2 in

Clear with Silver Mesh Print Glass Panel

Width: 20-1/8 in Height: 9-1/16 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Chain	10 feet of wire supplied	(3) Medium Base (E26) Socket	cETLus Damp Location Listed
1/8 IP mounting plate for outlet box included	120 VAC	Lamp Type G-25	1-year Limited Warranty
		Incandescent: 60-watt MAX per	
6 feet of 9 Gauge chain supplied		socket	
with quick linkCanopy covers a standard 4" recessed outlet box:		LED: 12.5-watt MAX per socket	
16" W., 1.125" ht., 5" depth		Fully dimmable with dimmable bulbs	