PROGRESS LIGHTING

Project:

Fixture Type:

Location:

Contact:

P550120-031 Chilton

Chilton Collection One-Light New Traditional Textured Black Etched Opal Glass Outdoor Hanging Light

Category: Outdoor Finish: Textured Black (Painted) Construction: Steel Construction Glass/Shade: Etched Opal Glass Cylindrical



Square: 11 in Height: 17-1/2 in Overall Ht. W/Chain: 92-1/2 in

Etched Opal Glass Cylindrical Width: 4-3/4 in Height: 10-3/8 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Chain	10 feet of wire supplied	(1) Medium Base (E26) Socket	cULus Damp Location Listed
1/8 IP mounting plate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
6 feet of 9 Gauge chain supplied with quick link		Incandescent: 100-watt MAX per socket LED: 17.5-watt MAX per socket	
Canopy covers a standard 4" recessed outlet box: 5" W., 1" ht., 5" depth		Fully dimmable with dimmable bulbs	