

Project:			
Fixture Type:			
Location:			
Contact:			

## P550122-020

## Dillard

Dillard Collection One-Light Traditional Antique Bronze Clear Glass Outdoor Hanging Light

Category: Outdoor

Finish: Antique Bronze (Painted)

Construction: Cast Aluminum Construction

Glass/Shade: Clear Glass Panel



Depth: 7-1/2 in Height: 13-5/8 in

Overall Ht. W/Chain: 52-1/2 in

Clear Glass Panel

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Chain	10 feet of wire supplied	(1) Medium Base (E26) Socket	cCSAus Damp Location Listed
1/8 IP mounting plate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
3 feet of 9 Gauge chain supplied		Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	
Canopy covers a standard 4" recessed outlet box: 5" W., 1" ht., 5" depth		Fully dimmable with dimmable bulbs	