

Project:

Fixture Type:

Location:

Contact:

## **P550127-31M** Pembroke

Category: Recessed

Finish: Matte Black (Painted) with Mocha Rattan accent

Construction: Steel Construction

Glass/Shade: Clear seeded Glass Cylindrical



Diameter: 20 in Height: 21-1/2 in

Overall Ht. W/Chain: 97 in

Clear seeded Glass Cylindrical

Width: 2-3/8 in Height: 6 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Chain	15 feet of wire supplied	(3) Candelabra Base (E12) Socket	cETLus Damp Location Listed
1/8 IP mounting plate for outlet box included	120 VAC	Lamp Type B10	1-year Limited Warranty
6 feet of 9 Gauge chain supplied with quick link		Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	
Canopy covers a standard 4" recessed outlet box: 5.12" W., 0.75" ht., 5.12" depth		Fully dimmable with dimmable bulbs	