

Project:

Fixture Type:

Location:

Contact:

P550128-31M

Swansea

Category: Recessed

Finish: Matte Black (Painted)
Construction: Steel Construction
Glass/Shade: Clear Glass Cylindrical



Square: 18 in Height: 17-1/4 in

Overall Ht. W/Chain: 92-1/2 in

Clear Glass Cylindrical Width: 2-3/4 in Height: 6 in

MOUNTING	FI FCTRICAI	LAMPING	ADDITIONAL INFORMATION
MOONTING	ELECTRICAL	LAWITING	ADDITIONAL IN ORMATION
Ceiling Chain	15 feet of wire supplied	(4) Candelabra Base (E12) Socket	cETLus Damp Location Listed
1/8 IP mounting plate for outlet box included	120 VAC	Lamp Type B10	1-year Limited Warranty
		Incandescent: 60-watt MAX per	
6 feet of 9 Gauge chain supplied		socket	
with quick link		LED: 12.5-watt MAX per socket	
Canopy covers a standard 4" recessed outlet box: 5.12" W., 0.75" ht., 5.12" depth		Fully dimmable with dimmable bulbs	