

Project: \_\_\_\_\_

Fixture Type: \_\_\_\_\_

Location: \_\_\_\_\_

Contact: \_\_\_\_\_

**P550129-31M**  
**Swansea**



**Category:** Recessed  
**Finish:** Matte Black (Painted)  
**Construction:** Steel Construction  
**Glass/Shade:** Clear Glass Cylindrical

Length: 36 in  
Width: 10-7/8 in  
Height: 11 in  
Overall Ht. W/Chain Or Stem: 77 in

Clear Glass Cylindrical  
Width: 4 in  
Height: 7-1/16 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Chain	15 feet of wire supplied	(4) Medium Base (E26) Socket	cETLus Damp Location Listed
1/8 IP mounting plate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
Two pieces of 6 links of 9 Gauge chain supplied (2) with quick links		Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	
Stem lengths (2) 6" and (8) 12" included		Fully dimmable with dimmable bulbs	
Canopy standard 4" recessed outlet box: 11.81" W., 0.81" ht., 4.75" depth			