

Project:		
Fixture Type:		
Location:		
Contact:		

P550131-031 Chapel

Chapel Collection Four-Light Textured Black Modern Farmhouse Outdoor Living Pendant

Category: Outdoor

Finish: Textured Black (Painted)
Construction: Steel Construction

Glass/Shade: Clear Seeded Glass Cylindrical



Square: 18-1/8 in Height: 22-1/8 in

Overall Ht. W/Chain: 85 in

Clear Seeded Glass Cylindrical

Width: 2-3/4 in Height: 6-1/8 in

		0 1	
MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling chain mounted	96 in of wire supplied	(4) Candelabra Base (E12) Socket	cULus Damp Location Listed
1/8 IP mounting plate for outlet box included	120 VAC	Lamp Type B10	1-year Limited Warranty
5 feet of 9 Gauge chain supplied with quick link		Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	
Canopy covers a standard 4" recessed outlet box: 5.12" W.,		Fully dimmable with dimmable bulbs	