



Project: \_\_\_\_\_  
 Fixture Type: \_\_\_\_\_  
 Location: \_\_\_\_\_  
 Contact: \_\_\_\_\_

## P550133-31M Keegan

Keegan Collection One-Light Matte Black Clear Glass Coastal Outdoor Flush Mount Light

**Category:** Outdoor  
**Finish:** Matte Black (Painted)  
**Construction:** Steel Construction  
**Glass/Shade:** Clear Glass Cylindrical



Diameter: 9-3/4 in  
 Height: 8-5/8 in

Clear Glass Cylindrical  
 Width: 6-9/16 in  
 Height: 11-11/16 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling mounted	6 inches of wire supplied	(1) Medium Base (E26) Socket	cCSAus Damp Location Listed
Mounting strap for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
Canopy covers a standard 4" recessed outlet box: 4.75" W., 0.75" ht., 4.75" depth		Incandescent: 100-watt MAX per socket LED: 17.5-watt MAX per socket Fully dimmable with dimmable bulbs	