

Project:		
Fixture Type:		
Location:		
Contact:		

## P550134-31M

## Keegan

Keegan Collection One-Light Matte Black Clear Glass Coastal Outdoor Hanging Lantern

Category: Outdoor

Finish: Matte Black (Painted)
Construction: Steel Construction
Glass/Shade: Clear Glass Cylindrical



Diameter: 13 in Height: 9-5/8 in

Overall Ht. W/Chain: 72.5 in

Clear Glass Cylindrical Width: 6-9/16 in Height: 11-11/16 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling chain mounted	96 in of wire supplied	(1) Medium Base (E26) Socket	cULus Damp Location Listed
Swivel Crossbar	120 VAC	Lamp Type A19	1-year Limited Warranty
5 feet of 9 Gauge chain supplied		Incandescent: 100-watt MAX per socket	
Canopy covers a standard 4" recessed outlet box: 5.12" W.,		LED: 17.5-watt MAX per socket	
0.75" ht., 5.12" depth		Fully dimmable with dimmable bulbs	