



Project: \_\_\_\_\_

Fixture Type: \_\_\_\_\_

Location: \_\_\_\_\_

Contact: \_\_\_\_\_



## P550136-31M Parrish

Parrish Collection Two-Light Matte Black Clear and Etched Glass Modern Craftsman Outdoor Flush Mount

**Category:** Outdoor  
**Finish:** Matte Black (Painted)  
**Construction:** Steel Construction  
**Glass/Shade:** Clear Glass Panel

Square: 11 in  
Height: 4-5/8 in

Clear Glass Panel

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Flush	6 inches of wire supplied	(2) Medium Base (E26) Socket	cCSAus Damp Location Listed
1/8 IP mounting plate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
Ceiling Pan covers a standard 4" recessed outlet box: 11" W., 1.25" ht., 11" depth		Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket Fully dimmable with dimmable bulbs	