

Project:			
Fixture Type:			
Location:			
Contact:			

## P550138-169

## **Bradshaw**

Bradshaw Collection One-Light Antique Copper Clear Glass Transitional Outdoor Hanging Lantern

Category: Outdoor

Finish: Antique Copper (Painted) Construction: Steel Construction Glass/Shade: Clear Glass Panel



Square: 12 in Height: 25-5/8 in

Overall Ht. W/Stem And Swivel: 82.5 in

Clear Glass Panel

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Stem Hung with Swivel	96 in of wire supplied	(1) Candelabra Base (E12) Socket	cULus Damp Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type B10	1-year Limited Warranty
One 6", four 12" lengths of stem included		Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	
Canopy covers a standard 4" recessed outlet box: 4.5" W., 0.75" ht., 4.5" depth		Fully dimmable with dimmable bulbs	