

3IN Cylinders

Ceiling Mounted • Damp Location Listed **PROGRESS LED**

Description:

3" White Surface Mount Modern Adjustable LED Cylinder

Specifications:

- Glass Glass Round Lens
- Dimmable to 10% brightness (See Dimming Notes)
- Canopy covers a standard 4" recessed outlet box: 5.1 in W., 1.3 in ht., 5.1 in depth
- Mounting Plate
- 6 in of wire supplied

Performance:

Number of Modules	1 Directional
Input Power	12 W
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW (Delivered)	986/82 (LM-79)
CCT	3000 K
CRI	90 CRI
Life (hours)	50000 (L70/TM-21)
EMI/RFI	FCC Title 47, Part 15, Class B
Warranty	5-year Limited Warranty
Labels	cCSAus Damp Location Listed
	Meets California Title 24 JA8-2016

P550139-030-30



Dimensions:

Diameter: 5.09 in
Height: 7-3/8 in

Glass Glass Round Lens
Diameter: 3.084 in
Height: 0-1/8 in



Dimming Notes:

P550139-030-30 is designed to be compatible with many ELV/Reverse Phase Triac/Forward Phase controls.

The following is a partial list of known compatible dimmer controls.

Dimming Controls:

Lutron_Diva DVELV-300P

Lutron_Diva DVELV-300P

Lutron_Caseta Wireless

Leviton_SureSlide 6672

Lutron_Ariadni AYCL-153P

Lutron_Toggler TGCL-153PH-WH

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation.

Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.

P550139-030-30