

Project:

Fixture Type:

Location:

Contact:

P550140-020 3IN Cylinders

3" Antique Bronze Surface Mount Modern Adjustable Cylinder

Category: Directional

Finish: Antique Bronze (Painted) with Bronze accent

Construction: Aluminum Construction



Diameter: 5 in Height: 7-3/8 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling mounted	6 inches of wire supplied	(1) Medium Base (E26) Lamp Type A19 or Par20	cCSAus Damp Location Listed
Mounting Plate	120 V	Incandescent: 60-watt MAX	1-year Limited Warranty
Canopy covers a standard 4" recessed outlet box: 5.1" W., 1.3"		per socket	
ht., 5.1" depth		Fully dimmable with dimmable bulbs	