

Project:			
Fixture Type:			
Location:			
Contact:			

## P550141-31M Unison

Unison Collection One-Light Matte Black Etched Seeded Glass Contemporary Hanging Lantern

Category: Outdoor

Finish: Matte Black (Painted)
Construction: Steel Construction
Glass/Shade: Etched Seeded Glass Panel



Square: 7 in Height: 19-3/8 in

Overall Ht. W/Chain: 92 in

Etched Seeded Glass Panel

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling chain mounted	10 feet of wire supplied	(1) Medium Base (E26) Socket	cULus Damp Location Listed
1/8 IP mounting plate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
		Incandescent: 100-watt MAX per	
6 feet of 9 Gauge chain supplied		socket	
with quick link		LED: 17.5-watt MAX per socket	
Canopy covers a standard 4" recessed outlet box: 4.5" W., 0.75" ht., 4.5" depth		Fully dimmable with dimmable bulbs	