

DATE:	TYPE:
NAME:	
PROJECT:	

Incandescent

P5503-108

Penfield

Smooth contemporary curves highlighted by a clear glass exterior surrounding an opal glass interior. Aluminum and brass construction. One-light hanging lantern .

Category: Outdoor

Finish: Oil Rubbed Bronze (painted)

Construction:

Glass: Outer clear glass cylinder, Inner white opal glass cylinder



Diameter: 8" Height: 14-1/4"

Overall ht. w/chain: 89-1/4"

Glass: 6-1/4" dia. Height: 10" Glass (2nd): 5" dia. Height: 10-3/8"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling chain mounted Mounting strap for outlet box included Six feet 9 gauge chain supplied	Pre-wired 15 feet of wire supplied 120V	Quantity: 1 100W Medium Base Medium porcelain socket	UL-CUL Damp location listed 1 year warranty Companion fixtures are available