

DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____

Incandescent

P5511-16

Cast Aluminum

One-light wall fixture with threaded opal glass shades that screw onto fitter. Vapor-proof gaskets and porcelain sockets. Satin Aluminum finish.

- Satin aluminum finish.
- Threaded opal glass shades.
- Modern outdoor look.

Category: Outdoor

Finish: Satin Aluminum (powder coat paint)

Construction: Cast aluminum Construction

Glass/Shade: White opal glass cylindrical diffuser



Width: 4-1/2"

Height: 7"

Depth: 5-7/8"

H/CTR: 3-1/4"

Glass

Width: 3-3/4"

Height: 6-5/16"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
<p>Wall mounted</p> <p>Mounting strap for outlet box included</p> <p>Back plate covers a standard 4" octagonal recessed outlet box</p> <p>4.5" W., 6" ht., 3.4375" depth</p>	<p>Pre-wired</p> <p>6" of wire supplied</p> <p>120 V</p>	<p>Quantity:</p> <p>One 100w max. Medium Base</p> <p>E26 base porcelain socket</p>	<p>UL-CUL Wet location listed</p> <p>1 year warranty</p>