

TYPE:

DATE:

NAME:

PROJECT:

Incandescent

P5511-31

Cast Aluminum

One-light wall fixture with threaded opal glass shades that screw onto fitter. Vapor-proof gaskets and porcelain sockets. Black finish.

- Black finish.
- Threaded opal glass shades.
- Modern outdoor look.

Category: Outdoor Finish: Black (powder coat paint) Construction: Cast aluminum Construction Glass/Shade: White opal glass cylindrical diffuser



Width: 4-1/2" Height: 7" Depth: 5-7/8" H/CTR: 3-1/4"

Glass Width: 3-3/4" Height: 6-5/16"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	Pre-wired	Quantity:	UL-CUL Wet location listed
Mounting strap for outlet box included Back plate covers a standard 4" octagonal recessed outlet box 4.5" W., 6" ht., 2.121" depth	6" of wire supplied 120 V	One 100w max. Medium Base E26 base porcelain socket	1 year warranty