

DATE: \_\_\_\_\_ TYPE: \_\_\_\_\_

NAME: \_\_\_\_\_

PROJECT: \_\_\_\_\_

Incandescent

# P5582-30

## Welbourne

The Welbourne collection features hexagonal framework with vine inspired scrolls and clear beveled glass panels. Cast aluminum construction with durable powder coat finish. One-light hanging lantern.

- Hexagonal framework.
- Vine inspired scrolls.
- Clear beveled glass panels.

**Category:** Outdoor

**Finish:** Textured White (painted)

**Construction:** Die-cast aluminum construction

**Glass/Shade:** Clear Beveled glass panels



**Diameter:** 9-3/8"

**Height:** 14-1/16"

**Overall Ht. W/Chain:** 53"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling chain mounted Mounting strap for outlet box included Three feet of 9 gauge chain supplied Canopy covers a standard 4" octagonal recessed outlet box 4.5" W.	Pre-wired 10 feet of wire supplied 120 V	Quantity: One 100w max. Medium Base E26 base porcelain socket	UL-CUL Damp location listed 1 year warranty