

DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____

Incandescent

P560004-135

Union Square

Union Square features a reproduction gas lantern inspiration. The wall lantern features a Stainless Steel finish which complements the natural polished material and clear flat glass panels. Mechanical details – such as exaggerated knobs – provide character to the form. Open bottom design allows easy access to replace lamp.

- Stainless Steel finish
- Gas lantern inspired
- Clear flat glass panels
- Mechanical details provide character
- Open bottom design for easy relamping

Category: Outdoor

Finish: Stainless Steel (painted)

Construction: Stainless steel construction

Glass/Shade: Clear flat glass panels



Width: 6-1/2"
Height: 15-7/8"
Depth: 5-1/2"
H/CTR: 6-1/4"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted Mounting strap for outlet box included Backplate covers a standard 4" hexagonal recessed outlet box 4" W., 4.5" ht., 0.8125" depth	Pre-wired 6" of wire supplied 120 V	Quantity: One 100w max. Medium Base E26 base ceramic socket	cCSAus Wet location listed 1 year warranty