

Project:

Fixture Type:

Location:

Contact:

P560005-169

Union Square

Union Square One-Light Medium Antique Copper Urban Industrial Outdoor Wall Lantern

Category: Outdoor

Finish: Antique Copper (Painted) with Matte Black accent

Construction: Steel Construction **Glass/Shade:** Clear Glass Panel



Width: 7-7/8 in Extends: 6-1/2 in Height: 19-3/8 in H/CTR: 7-3/4 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(1) Medium Base (E26) Socket	cCSAus Wet Location Listed
Mounting backplate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
Canopy covers a standard 4"		Incandescent: 100-watt MAX per socket	
recessed outlet box: 5.5" W., 0.81" ht., 5.5" depth		LED: 17.5-watt MAX per socket	
,		Fully dimmable with dimmable bulbs	