

DATE:

TYPE:

NAME:

PROJECT:

Incandescent

P560006-135

Union Square

Union Square features a reproduction gas lantern inspiration. The wall lantern features a Stainless Steel finish which complements the natural polished material and clear flat glass panels. Mechanical details – such as exaggerated knobs – provide character to the form. Open bottom design allows easy access to replace lamp.

- Stainless Steel finish
- Gas lantern inspired
- Clear flat glass panels
- Mechanical details provide character
- Open bottom design for easy relamping

Category: Outdoor

Finish: Stainless Steel (painted)

Construction: Stainless steel construction

Glass/Shade: Clear flat glass panels



Width: 9-3/4" Height: 23-5/8" Depth: 8" H/CTR: 9-5/8"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	Pre-wired	Quantity:	cCSAus Wet location listed
Mounting strap for outlet box included Backplate covers a standard 4" hexagonal recessed outlet box 6.5" W., 7" ht., 0.8125" depth	6" of wire supplied 120 V	One 100w max. Medium Base E26 base ceramic socket	1 year warranty